



PRAISTON Sp. z o.o.
ul. Górowska 32
64-100 Leszno
Polska

Biuro: +48 65 527 01 67
Serwis: +48 782 844 000
Fax: +48 65 527 01 67

E-mail: biuro@praiston.pl

Koordinator ds. sprzedaży
Krzysztof Wybieralski
+48 882 762 006

kw@praiston.pl



SELIGA OPTILION CSA operating microscope (Reconditioned)

Reconditioned (used),
Technical condition: very good,
Visual condition: very good,
Real photos of the product,
Polish production,
Power supply: 230 V,
Frequency: 50/60 Hz,
Power: 175 W,
Bulb: 15 V / 150 W,
OPTILION CSA
by SELIGA is a microscope with a very solid and stable construction. The simple design and small size make the microscope suitable for use even in small offices,
Specifications:
Binocular with fixed tilt angle: 45°,
Focal length: f=250,
Magnification adjustment with knob: 0.6x / 1.0x / 1.6x / 2.5x,
Magnification eyepiece: 12.5x,
Freely adjustable eyepiece spacing,
Built-in filter: green / orange / neutral filter,
Full manual adjustment of head spacing vertically and horizontally with free rotation around its axis,
Electrically controlled focus via foot switch gives the operator real comfort when working in the treatment field. This is especially important when the depth of field, at the highest magnification, is less than the vertical dimension of the anatomical structure being viewed,
The microscope is equipped with a light source with a built-in 15 V / 150 W halogen bulb with 4-stage adjustment of the light source intensity,
Placed on a mobile base with 4 braking casters,
Included:
Power cord,
Wired foot controller,
Dimensions:
Base: 56 x 60 cm,
Column height: 138 cm,
Max. height from floor to lens: 145 cm,
Min. height from floor to lens: 109 cm,
Arm reach with power supply and head: 128 cm,
Arm length: 62 cm,
Head height: 21 cm,
Weight: 85 KG,
It has a current inspection and is ready to work,
Issued Technical Passport (Service Report) valid for 12 months,
Warranty:
6-months for domestic market (Poland),
3-months for the international market,
Possibility to extend the warranty at a surcharge to 12-months for domestic and international markets,
The warranty period does not include bulbs and other light sources installed in the device,
Possibility of financing (Poland only): Installments, Leasing, Loan,

