



PRAISTON Sp. z o.o.
ul. Górowska 32
64-100 Leszno
Polska

Biuro: +48 65 527 01 67
Serwis: +48 782 844 000
Fax: +48 65 527 01 67

E-mail: biuro@praiston.pl

Koordinator ds. sprzedaży
Krzysztof Wybieralski
+48 882 762 006

kw@praiston.pl



ARL ZEISS LUMERA 300 operating and surgical microscope (Reconditioned)

Reconditioned (used),
Technical condition: very good,
Visual condition: very good,
Real photos of the product,
German production, (2021),
Power supply: 230 V,
Frequency: 50/60 Hz,
ZEISS OPMI LUMERA 300
is an advanced surgical microscope, both in terms of optics and light, designed for cataract and retinal surgery.
The BRA IGH T FLEX LED illumination technology that was used together with the apochromatic optics provides exceptional visibility and resolution,
BrightFlex technology, a variable electronic LED, reduces red reflux for more effective cataract surgery,
This microscope provides exceptional clarity and image detail while reducing patient exposure to light,
Technical specifications:
5-stage apochromatic magnification adjustment (manual and electric),
Magnification factor: x0.4 / x0.6 / x1.0 / x1.6 / x2.5,
Focusing range: 48 mm,
Lens focal length: f = 200 APO,
Free vertical adjustment and horizontal rotation tube,
Eyepiece: 12.5x (wide angle),
Filters:
Color enhancement,
Ha mode,
Blue blocking,
Adjustable 2-segment arm with 360° rotation,
Free vertical adjustment of the eyepiece arm and 150° rotation,
Microscope placed on a mobile base,
Possibility to electrically control the microscope head functions with a wired foot controller,
Included:
Instruction manual in Polish,
Power cord,
Dimensions:
Overall height: 173.5 cm,
Span of 2-segment arm: 110 cm,
Screw set for mounting additional accessories,
(2 packs) new 6x sterile 27mm sockets...,
(3 packs) new 6x sterile sockets 22mm...,
New 6x sterile sockets 49mm...,
New 4x sterile caps for handles,
Wired foot controller,
Weight: 160 KG,
Has a current inspection and is ready for use,
Issued Technical Passport (Service Report) valid for 12 months,
Warranty:
6-months for domestic market (Poland),
3-months for the international market,
Possibility to extend the warranty at a surcharge to 12-months for domestic and international markets,
The warranty period does not include bulbs and other light sources installed in the device,
Possibility of financing (Poland only): Installments, Leasing, Loan,

