



**PRAISTON Sp. z o.o.**  
ul. Górowska 32  
64-100 Leszno  
Polska

Biuro: +48 65 527 01 67  
Serwis: +48 782 844 000  
Fax: +48 65 527 01 67

E-mail: [biuro@praiston.pl](mailto:biuro@praiston.pl)

Koordynator ds. sprzedaży  
Krzysztof Wybieralski  
+48 882 762 006

[kw@praiston.pl](mailto:kw@praiston.pl)



## **DRAGER SOLA 500 MOBIL operating lamp (Reconditioned)**

Reconditioned (used),  
Technical condition: very good,  
Visual condition: very good,  
Real photos of the product,  
German production,  
Power supply: 230 V,  
Emergency power supply: via 2 new built-in 12 V / 7.2 Ah batteries,  
Frequency: 50/60 Hz,  
Bulb: 22.8 V / 110 W,  
Specifications:  
Color temperature: 4200 K,  
Illuminance. Ec at 1 m [KLX] 90 / 90000 lux,  
Color reproduction index: 95% ,  
Light emission intensity: 320 W/m  
2

,  
Focal length adjustment between: 150-230 mm,  
On the lamp arm - lamp switch and light intensity adjustment (50-100% ),  
Removable autoclavable handle,  
Infinitely adjustable lamp canopy height in the range: 71 to 185 cm,  
Infinitely adjustable tilt of the lamp canopy,  
Mobile base on wheels (2 braking wheels),  
Included:  
Power cord,  
Autoclavable holder (2 pcs),  
Dimensions:  
Diameter of the lamp body: 50 cm,  
Base: 78 x 70 cm,  
Height of the arm mounting mast: 200 cm,  
Arm length: 90 cm,  
Highest point of the lamp arm: 245 cm,  
It has a current inspection and is ready for operation,  
Issued Technical Passport (Service Report) valid for 12 months,  
Warranty:  
6-months for domestic market (Poland),  
3-months for the international market,  
Possibility to extend the warranty at a surcharge to 12-months for domestic and international markets,  
The warranty period does not include bulbs and other light sources installed in the device,  
Possibility of financing (Poland only): Installments, Leasing, Loan,

