



**PRAISTON Sp. z o.o.**  
ul. Górowska 32  
64-100 Leszno  
Polska

Biuro: +48 65 527 01 67  
Serwis: +48 782 844 000  
Fax: +48 65 527 01 67

E-mail: [biuro@praiston.pl](mailto:biuro@praiston.pl)

Koordinator ds. sprzedaży  
Krzysztof Wybieralski  
+48 882 762 006

[kw@praiston.pl](mailto:kw@praiston.pl)



## **DRAGER SOLA 700 operating lamp (Reconditioned)**

Reconditioned (used),  
Technical condition: very good,  
Visual condition: very good,  
Real photos of the product,  
German production,  
Power supply: 230 V,  
Frequency: 50/60 Hz,  
Halogen bulb 24 V / 150 W (2 pcs.),  
Technical specifications:  
Color temperature: 4200 K,  
Illuminance. Ec per 1 m [KLX] 145, 145000 lux,  
Color reproduction index: 95% ,  
Light emission intensity: <600 W/m  
2

Focal length adjustment between: 150-260 mm,  
On the lamp arm - lamp switch and light intensity adjustment (50-100% ),  
Halogen bulb: 24 V / 150 W,  
Diameter of the lamp body: 70 cm,  
Removable autoclavable handle,  
Free adjustment of tilt and rotation of the lamp canopy,  
Free adjustment of the rotating 2-segment arm horizontally and vertically,  
Minimum proper ceiling height: 280 cm,  
Can be retrofitted with a dedicated mounting bezel at an additional cost,  
Includes:  
Autoclavable bracket (2 pcs),  
Transformer,  
Dimensions:  
Total width of the canopy: 70 cm,  
Spacing of 2-segment arm: 180 cm,  
Total weight: 60 KG,  
Has a current inspection and is ready for operation,  
Issued Technical Passport (Service Report) valid for 12 months,  
Warranty:  
6-months for domestic market (Poland),  
3-months for the international market,  
Possibility to extend the warranty at a surcharge to 12-months for domestic and international markets,  
The warranty period does not include bulbs and other light sources installed in the device,  
Possibility of financing (Poland only): Installments, Leasing, Loan,

