



PRAISTON Sp. z o.o.
ul. Górowska 32
64-100 Leszno
Polska

Biuro: +48 65 527 01 67
Serwis: +48 782 844 000
Fax: +48 65 527 01 67

E-mail: biuro@praiston.pl

Koordinator ds. sprzedaży
Krzysztof Wybieralski
+48 882 762 006

kw@praiston.pl



TOPCON SL-3F Slit Lamp (Reconditioned)

Reconditioned (used),
Technical condition: very good,
Visual condition: very good,
Actual product photos,
Made in Japan,
Power supply: 230 V,
Frequency: 50/60 Hz,
Halogen bulb: 8 V / 20 W,
Slit lamp
TOPCON SL-3F
placed on a mobile table with electric tabletop height adjustment within a range of 70 – 90 cm,
Slit lamp equipped with an applanation tonometer
HAAG-STREIT R90017681, which is used in ophthalmology to measure intraocular pressure – one of the key elements in the diagnosis and effective treatment of glaucoma. Characterized by high measurement precision and repeatability of obtained results,
Specifications:
Eyepieces with magnification: 10x,
Rotating eyepiece (lamp): 90°,
Illumination of the anterior segment of the eye,
Magnification adjustment: 1.0x, 1.6x,
Focus adjustment from -8 to +8 D,
Smooth slit width adjustment: 0 - 20 (according to the scale),
Smooth slit length adjustment: 0.2/1/2/3/5/8/9 (according to the scale),
Smooth slit length adjustment: 1 - 8 (according to the scale),
Smooth slit rotation adjustment relative to the optical axis up to 90° in any direction, which, combined with a wide range of slit settings, allows for distance assessment in any plane,
Smooth adjustment of the patient's chin within a range of: 10 cm,
Smooth lamp height adjustment within a range of: 3 cm using a knob,
Smooth adjustment of light intensity using a knob,
4 built-in filter types:
Blue filter,
Red-free filter,
13% ND filter,
Heat absorption filter,
Included:
HAAG-STREIT R90017681 Applanation Tonometer,
Power cord,
Dimensions:
Slit lamp: 31 x 32.5 x 67 cm,
Total: 64 x 50 x 140 / 160 cm,
Weight: 40 kg,
Updated inspection and ready for use,
Issued Technical Passport (Service Report) valid for 12 months,
Warranty:
6 months for the domestic market (Poland),
3 months for the international market,
Possibility to extend the warranty for an additional fee. 12 months for domestic and international markets.
The warranty period does not cover light bulbs and other light sources installed in the device.
Financing options (Poland only): Installments, Leasing, Loan.

