



PRAISTON Sp. z o.o.
ul. Górowska 32
64-100 Leszno
Polska

Biuro: +48 65 527 01 67
Serwis: +48 782 844 000
Fax: +48 65 527 01 67

E-mail: biuro@praiston.pl

Koordinator ds. sprzedaży
Krzysztof Wybieralski
+48 882 762 006

kw@praiston.pl



SIEMENS ACUSON X300 ultrasound machine (Reconditioned)

- Reconditioned (used),
- Technical condition: very good,
- Visual condition: very good,
- **Real product photos,**
- Korean production,
- Power supply: 230 V,
- Frequency: 50/60 Hz,
- **The ACUSON X300** is a fully digital, mobile ultrasound system designed for a full spectrum of clinical applications. The system operates in 2D, M-mode, PW Doppler, Power Doppler, and Color Doppler modes, making it suitable not only for basic diagnostics but also for cardiology and vascular examinations. Furthermore, thanks to the use of numerous modern technologies, such as Multibeam Formation (enabling image formation using multiple beams) and MultiHertz (imaging using multiple frequencies), it ensures the highest imaging quality in its class. The ACUSON X300 is equipped with a 15-inch flat-panel monitor and an integrated DIMAQ-IP archiving system, enabling the storage of examinations on a built-in hard drive, CD/DVD, or USB storage media.
- **Imaging modes:**
 - **SINGLE MODE:**
 - 2D dual and split mode with fundamental and harmonic imaging THI,
 - M-mode,
 - Color Doppler mode,
 - Doppler power mode,
 - PW Doppler (pulse Doppler mode),
 - **MIXED MODES:**
 - 2D/M mode,
 - 2D/Doppler mode,
 - 2D mode with color, (2D mode with power),
 - 2D mode with color Doppler (update and triplex),
 - 2D mode with power/Doppler (update and triplex),
 - 4B mode with color (4B mode with power)
 - M mode with color,
 - Flexible combination of real-time imaging modes,
- **Equipped with:**
 - 15-inch high-resolution color flat-screen display with progressive scanning IPS technology; 1024 x 768 pixel resolution, multi-directional articulating monitor arm for improved ergonomics.
 - Two active transducer ports and one resting port,
 - DICOM function, network connectivity,
 - Illuminated control panel,
 - ECG Port,
 - CD-RW/DVD-RW reader,
 - USB ports,
 - RS-232C ports - for transferring data to a personal computer,
 - RGB, VGA output,
 - S-VHS Input/Output, Y/C Input,
 - VHS Input/Output(BNC).
 - Audio Input/Output,
 - Accessory power socket,
 - Probe and gel holders,
 - MITSUBISHI P95 laser printer,
- **Possibility to select menu in: ENG, GER, FR, ESP, IT,**
- **Included in the set:**
 - User manual in Polish (PDF),
 - Convex head SIEMENS CH5-2,
 - SIEMENS VF10-5 linear head,
 - Power cord,
- Dimensions: 50 x 85 x 142 cm,
- Weight: 85 KG,
- Cat 03,
- **It has a current inspection and is ready to work,**
- **Issued Technical Passport (Service Report) valid for 12 months,**
- **Guarantee:**
 - **6 months for the domestic market (Poland),**
 - **3 months to the international market,**
 - **Possibility of extending the warranty for an additional fee up to 12 months for the domestic and international markets,**
- Financing options (Poland only): Installments, Leasing, Loan,

