



PRAISTON Sp. z o.o.
ul. Górowska 32
64-100 Leszno
Polska

Biuro: +48 65 527 01 67
Serwis: +48 782 844 000
Fax: +48 65 527 01 67

E-mail: biuro@praiston.pl

Koordinator ds. sprzedaży
Krzysztof Wybieralski
+48 882 762 006

kw@praiston.pl



OPTON 30 SL-M slit lamp (Reconditioned)

Reconditioned (used),
Technical condition: very good,
Visual condition: very good,
Actual product photos,
Made in Germany,
Power supply: 230 V,
Frequency: 50/60 Hz,
Light source: 12 V / 30 W halogen bulb,
Opton 30 SL - M
is a slit lamp used for examining eye structures.
Built-in fixation point and diverging lens.
Features the following filters:
Green,
Yellow,
Blue.
Specifications:
Eyepiece correction: (-5) / 0 / 5,
Focal length (f): 125,
Magnifications: 5x / 8x / 12x / 20x / 30x,
Smooth adjustment of:
Slit width,
Slit rotation,
Lamp height within 3 cm using Joystick,
Patient's chin within a range of 5.5 cm,
Interpupillary distance,
Light intensity,
6-stage slit height adjustment,
Device placed on a table with manual tabletop height adjustment within a range of 72 – 87 cm,
Includes:
Power cord,
Dimensions:
Lamps: 40 x 27.5 x 48 cm,
Total dimensions: 60 x 40 x 135 cm,
Weight: 60 kg,
Valid inspection and ready for operation,
Issued Technical Passport (Service Report) valid for 12 months,
Warranty:
6 months for the domestic market (Poland),
3 months for the international market,
Possibility of extending the warranty for an additional fee to 12 months for the domestic and international markets,
The warranty period does not cover bulbs and other light sources installed in the device. device,
Financing options (Poland only): Installments, Leasing, Loan,

