



PRAISTON Sp. z o.o.
ul. Górowska 32
64-100 Leszno
Polska

Biuro: +48 65 527 01 67
Serwis: +48 782 844 000
Fax: +48 65 527 01 67

E-mail: biuro@praiston.pl

Koordinator ds. sprzedaży
Krzysztof Wybieralski
+48 882 762 006

kw@praiston.pl



Ophthalmometer (perimeter) OCULUS CENTERFIELD 2 (Reconditioned)

Refurbished (used),
Technical condition: very good,
Visual condition: very good,
Real product photos,
German manufacture,
Power supply: 230 V,
Frequency: 50/60 Hz,
Software: V3.19,
OCULUS CENETRFIELD 2
is an ophthalmometer projection device used for static and kinetic visual field testing.
The device also allows testing with a blue stimulus on a yellow background (blue on yellow test). It fully complies with the Goldmann standard and meets the requirements of the international perimetry standard ISO-12866,
Specification:
Programs:
Glaucoma screening,
Glaucoma localization,
Glaucoma threshold,
Macula screening,
Macula threshold,
Esterman,
Driver’s test,
Individual,
Test patterns:
Orthogonal patterns (30-2 / 24-2 / 30 x 24 / 10-2),
Physiological patterns (area 1-8),
Esterman,
Customized patterns,
Strategies:
Classical suprathreshold,
Two-field suprathreshold,
Three-field suprathreshold,
Suprathreshold with defect assessment,
Fast threshold,
Threshold,
CLIP,
Equipment:
Medical computer ACL OR-PC19LP:
Display:
Resolution: 1280 x 1024 px,
Contrast 1500:1,
Brightness 300 cd/m²,
Viewing angle: 178°/178°,
System: WINDOWS 10 PRO,
Processor: i5-4300U 1.90 GHz,
RAM: 4.00 GB,
Disk: 112 GB,
Integrated graphics card,
Printer CANON MP282,
Accessories placed on a mobile table
CARL ZEISS IT3F
with electric height adjustment 67 – 96 cm,
Language menu option: ENG, DE, FR, ES, CS, CHIN, PL, PT, RUS,
Included:
Power cable,
Wireless mouse LOGITECH,
Wireless keyboard LOGITECH,
Patient button,
Printer CANON MP282,
Overall dimensions: 95 x 45 x 125 cm,
Weight: 80 KG,
Has current inspection and is ready for use,
Technical Passport (Service Report) issued and valid for 12 months,
Warranty:
6 months for domestic market (Poland),
3 months for international market,
Warranty extension available for up to 12 months for domestic and international markets for an additional fee,
Warranty period does not cover bulbs and other light sources installed in the device,
Financing options (Poland only): Installments, Leasing, Loan,

