



PRAISTON Sp. z o.o.
ul. Górowska 32
64-100 Leszno
Polska

Biuro: +48 65 527 01 67
Serwis: +48 782 844 000
Fax: +48 65 527 01 67

E-mail: biuro@praiston.pl

Koordinator ds. sprzedaży
Krzysztof Wybieralski
+48 882 762 006

kw@praiston.pl



Non-contact tonometer NIDEK NT-4000 (Reconditioned)

Refurbished (used),

Technical condition: very good,

Visual condition: very good,

Real product photos,

Made in Japan,

Power supply: 230 V,

Frequency: 50/60 Hz,

Power: 70 VA,

Non-contact tonometer

NIDEK NT-4000

includes all features of model NT-2000, and in addition the "pulse synchronization" system reducing fluctuations and enabling more accurate measurements,

The operator can turn on heart rate synchronization by pressing the switch, and NT-4000 will record peak heart rate values to eliminate systolic or diastolic pressure fluctuations. After activating this feature, noise caused by heart beating is eliminated, and actual intraocular pressure (IOP) changes are identified,

Printer: thermal line printer Operator can choose between three operating modes: fully automatic, semi-automatic and manual,

Auto focus range extended by over 50% toward focusing, which allows faster and more convenient measurements,

Specification:

Tonometer measurement range: 1 to 60 mmHg - 1 mmHg steps,

Measurement range setting: APC40 / APC60 / 40 / 60,

Tonometer working distance: 11 mm,

Auto pulling control function (APC): Yes

Intraocular pressure measurement synchronized with pulse: Yes,

Eyelid detection function: Yes,

Display: 5-inch color TFT display,

Thermal line printer,

Menu language: English,

In the package:

Power cord,

Dimensions: 26 x 48.7 x 45.7 cm,

Weight: 17 KG,

Has current inspection and is ready for use,

Technical Passport (Service Report) issued and valid for 12 months,

Warranty:

6 months for domestic market (Poland),

3 months for international market,

Possibility to extend warranty for an additional 12 months for domestic and international markets,

Warranty does not cover bulbs and other light sources installed in the device,

Financing options (Poland only): Installments, Leasing, Loan,

