



PRAISTON Sp. z o.o.
ul. Górowska 32
64-100 Leszno
Polska

Biuro: +48 65 527 01 67
Serwis: +48 782 844 000
Fax: +48 65 527 01 67

E-mail: biuro@praiston.pl

Koordinator ds. sprzedaży
Krzysztof Wybieralski
+48 882 762 006

kw@praiston.pl



Auto Kerato-Refractometer RC-800 TOMEY (Reconditioned)

Reconditioned (used),
Technical condition: very good,
Visual condition: very good,
Real photos of the product,
Japanese production, (2015),
Power supply: 230 V,
Frequency: 50/60 Hz,
Power: 100 VA,
Selectable menu in language: English,
Autokeratorefractometer RC
-800 performs high quality measurement combined with speed of examination and simplicity of operation, making working with the RC-800 is fast and professional,
The device can be operated and adjusted using a joystick and touch screen, all in an extremely short time,
All test parameters can be set on the 5.7" touch screen,
Operation
RC-800
is very easy to operate. Once the optical head is adjusted to the patient's eye, the measurement is performed automatically,
Technical specifications:
Refraction:
Contact lens measurement option,
PD of the patient - 50 to 86 mm,
VD of the patient - 0 - 16 mm,
Cylinders (CYL) - 0 to ± 10 D,
Form of cylinders +/-mix,
Sphere (SPH) - from -25 to +22 D,
Axis - from 1° to 180° ,
Minimum pupil size - 2 mm,
Keratometer:
Radius of curvature - 5 to 11 mm,
Corneal spherical power - 30.68 to 67.50 D,
CYL - 0 to ± 10 D,
Axis - from 0° to 180° ,
Corneal diameter measurement,
Has a built-in thermal printer,
Output port: RS232C, USB,
Device placed on a mobile electric table:
Height adjustment in range: 73 - 98 cm,
Built-in 2 sockets for powering additional equipment (230 V),
Mobile table on 4 casters (2 braking),
Includes:
User manual in Polish (PDF),
Power cord,
Dimensions:
Devices: 30 x 50 x 49 cm,
Table: 66 x 45 x 77/98 cm,
Weight: 17 KG,
Has a current inspection and is ready for use,
Issued Technical Passport (Service Report) valid for 12 months,
Warranty:
6-months for domestic market (Poland),
3-months for the international market,
Possibility to extend the warranty up to 12-months for domestic and international market for a surcharge,
Financing options (Poland only): Installments, Leasing, Loan,

