



PRAISTON Sp. z o.o.
ul. Górowska 32
64-100 Leszno
Polska

Biuro: +48 65 527 01 67
Serwis: +48 782 844 000
Fax: +48 65 527 01 67

E-mail: biuro@praiston.pl

Koordinator ds. sprzedaży
Krzysztof Wybieralski
+48 882 762 006

kw@praiston.pl



TOPCON SL-D7 slit lamp (Reconditioned)

Product temporarily unavailable
Reconditioned (used),
Technical condition: very good,
Visual condition: very good,
Real photos of the product,
Japanese production,
Power supply: 230 V,
Frequency: 50/60 Hz,
Light source: halogen bulb 12 V / 30 W,
TOPCON SL-D7 slit lamp
is a slit lamp used for examining the structures of the eye,
Technical specifications:
Gradual eyepiece correction: (-5) / 0 / 5,
Gradual eyepiece magnification: 6 / 10 / 16 / 25 / 40,
Eyepiece magnification: 12.5x,
Illumination area:
Slit width: 0 - 14 mm (changed gradually),
Slit length: 14 - 1 mm (changed gradually),
Slit diameter: \varnothing 14, 10, 5, 2, 1, 0.2,
Free light intensity adjustment,
Height adjustment of the tabletop in the range: 69 - 87 cm,
Forward - backward movement in range: 90 mm,
Left - right movement in range: 100 mm,
Vertical adjustment range: 30 mm,
Chin adjustment range: 8 cm,
Built-in following filters:
Cobalt,
Infrared-free,
Amber,
Neutral density,
Built-in fixation point with free horizontal movement,
Includes:
User manual in English (PDF),
Power cord,
Mobile operator table,
Pair of rubber eye rests for eyepiece,
Dimensions:
Operator table top: 60 x 45 cm,
Overall: 60 x 53 x 135/153 cm,
Total weight: 38 kg,
Has a current inspection and is ready to work,
Issued Technical Passport (Service Report) valid for a period of 12 months,
Warranty:
6-months for domestic market (Poland),
3-months for the international market,
Possibility to extend the warranty at a surcharge to 12-months for domestic and international markets,
The warranty period does not include bulbs and other light sources installed in the device,
Possibility of financing (Poland only): Installments, Leasing, Loan,

