



**PRAISTON Sp. z o.o.**  
ul. Górowska 32  
64-100 Leszno  
Polska

Biuro: +48 65 527 01 67  
Serwis: +48 782 844 000  
Fax: +48 65 527 01 67

E-mail: [biuro@praiston.pl](mailto:biuro@praiston.pl)

Koordinator ds. sprzedaży  
Krzysztof Wybieralski  
+48 882 762 006

[kw@praiston.pl](mailto:kw@praiston.pl)



## **HEINE BETA 200 Slit Retinoscope (Reconditioned)**

Refurbished (used),  
Technical condition: very good,  
Visual condition: very good,  
Real product photos,  
German manufacture,  
Power supply: 230 V,  
Power supply: battery 3.6 V / 1 Ah,  
Frequency: 50/60 Hz,  
Lamp: halogen 2.5 V,  
Skiascop BETA 200  
is used for precise refractive error measurement in myopia and hyperopia as well as astigmatism,  
High-quality metal construction for high stability and long service life,  
Specification:  
Easy adjustment of parallel beam path,  
Multilayer optics,  
Integrated polarizing filter eliminates scattered light and internal reflections,  
Wergence and rotation of the line are adjusted with a single knob,  
Strong halogen lamp,  
Ergonomic housing ensuring good coverage of the orbit and elimination of scattered light,  
Dust-tight construction,  
Holder for fixation cards,  
Has an up-to-date inspection and is ready for operation,  
Technical Passport (Service Report) valid for 12 months,  
Warranty:  
6 months on the domestic market (Poland),  
3 months on the international market,  
Option to extend the warranty for a surcharge to 12 months on the domestic and international market,  
Warranty period does not cover bulbs and other light sources installed in the device,  
Financing options (Poland only): Installments, Leasing, Loan,

