



**PRAISTON Sp. z o.o.**  
ul. Górowska 32  
64-100 Leszno  
Polska

Biuro: +48 65 527 01 67  
Serwis: +48 782 844 000  
Fax: +48 65 527 01 67

E-mail: [biuro@praiston.pl](mailto:biuro@praiston.pl)

Koordynator ds. sprzedaży  
Krzysztof Wybieralski  
+48 882 762 006

[kw@praiston.pl](mailto:kw@praiston.pl)



## **DRAGER DIGIFLOW AIR digital flowmeter (Reconditioned)**

- Reconditioned (used),
- Technical condition: very good,
- Visual condition: very good,
- **Real product photos,**
- German production,
- Powered by a built-in 3.6 V battery,
- **The DRAGER DigiFlow** device is designed based on modern sensor technology and a digital display,
- Flow measurement and settings are more precise than standard flow meters, and the regulators operate in smaller steps,
- **Characteristics:**
  - Accurate flow measurements,
  - Easy operation,
  - Clear reading of values,
- **Technical specifications:**
  - Parameter: standard (0-16 L/min),
  - Inlet pressure: 270-600 kPa (2.7-6 bar),
  - Flow range: 0-16 L/min,
  - Display range: 0.3-19.5 L/min.,
  - Flow restriction: approximately 20 L/min.,
  - Measurement accuracy:  $\pm 10\%$  of the reading value,
  - Display accuracy:  $\pm 1$  digit,
- **Flow meter prepared for humidifier,**
- **Included in the set:**
  - Hose with AGA / DIN connection (to be selected when purchasing),
- **It has a current inspection and is ready to work,**
- **Issued Technical Passport (Service Report) valid for 12 months,**
- **Guarantee:**
  - **6 months for the domestic market (Poland),**
  - **3 months to the international market,**
  - **Possibility of extending the warranty for an additional fee up to 12 months for the domestic and international markets,**
- Financing options (Poland only): Installments, Leasing, Loan,

