



PRAISTON Sp. z o.o.
ul. Górowska 32
64-100 Leszno
Polska

Biuro: +48 65 527 01 67
Serwis: +48 782 844 000
Fax: +48 65 527 01 67

E-mail: biuro@praiston.pl

Koordinator ds. sprzedaży
Krzysztof Wybieralski
+48 882 762 006

kw@praiston.pl



TOPCON TRC-NW7SF MARK-II Fundus Camera (Reconditioned)

Refurbished (used),
Technical condition: very good,
Visual condition: very good,
Actual product photos,
Made in Japan,
Power supply: 230 V,
Frequency: 50/60 Hz,
Power: 1500 VA,
Software: IMAGE NET – 3.8.0.,
Topcon TRC-NW7SF Mark II
combines fundus imaging with pupil dilation and without dilation in one system, combines in one system the possibilities of imaging the retina in mydriatic and non-mydriatic modes. The Topcon TRC-NW7SF is designed to perform a wide range of procedures. Imaging capabilities of the TRC-NW7SF include color angiography, non-red (gray) and fluorescein angiography. Intended for ophthalmologists with versatile applications, enabling high-quality imaging,
TRC-NW7SF
also offers simple, ergonomic control, making the system highly intuitive and easy to operate.
The device is designed to take retinal photos including:
Color photographs,
Red-free images (non-red),
Fluorescein angiography,
Features:
Medical-grade image sensor ensuring accurate color reproduction,
Rotational movement and tilt allow precise imaging of peripheral parts of the retina,
Ability to take photos without pupil dilation (starting from 3 mm for color mode),
Intuitive operation thanks to ergonomic construction,
Integration with EyeRoute system,
Technical specifications:
Types of photography:
color photos,
with fluorescein angiography (FA),
with cobalt filter,
red-free photos,
IA,
Field of view:
30° ø 4.0 mm or larger,
45° ø 4.5 mm or larger,
50° ø 5.5 mm or larger,
Ranges of compensation for patient refractive error:
Without auxiliary lens: -13D to +12D,
With a “-” correcting lens: -33D to -12D,
With a “+” correcting lens: -9D to +40D,
Fixation types:
Internal:
Central 4 points,
Peripheral 8 points,
External articulated,
Easy Focus & Alignment (Sharpness and alignment are easily achieved by crossing vertical lines with dots),
Built-in 6.5" LCD screen,
Working distance: 40.7 mm,
Horizontal rotation range: right and left: 32.5°,
Base movement range: forward and backward 80 mm, left and right 110 mm, up 12 mm, down 30 mm,
Tilt angle up and down: up 15° / down 10°,
Chin rest adjustment range: 60 mm,
Seamless IMAGENet connectivity
Menu language: English,
Equipment:
PC workstation:
Software: WINDOWS XP,
Processor: INTEL PENTIUM E5200 2.50 GHz,
RAM: 2 GB,
Hard drive: 256 GB,
MONITOR: SAMSUNG 2233BW,
Articulated fixation point,
Accessories mounted on a mobile height-adjustable cart: 70 – 88 cm,
Included in the set:
MONITOR: SAMSUNG 2233BW,
PC workstation,
Keyboard and wired mouse,
Articulated fixation point,
Overall dimensions: 142 x 58 x 148 / 160 cm,
Weight: 100 KG,
Has current inspection and is ready for use,
Technical Passport (Service Report) valid for 12 months,
Warranty:
6 months for the domestic market (Poland),
3 months for the international market,
Option to extend warranty for an additional 12 months for domestic and international markets,
Warranty period does not cover bulbs and other light sources installed in the device,
Financing options (only Poland): Installments, Leasing, Loan,

