



Video System Center PENTAX EPM 3000 (Reconditioned)

- Condition: Reconditioned - Very Good,
- Power input: 230 V,
- Frequency: 50 - 60 Hz,
- Power: 700 VA,
- Xenon 300 W type: Y1089,
- Color Saturation: Red/Blue,
- Adjustable brightness,
- Air pump,
- Freeze function,
- Sealed control panel,
- Dimensions: 49,5 x 22 x 54 cm,
- Weight: 32 kg,
- Technical Passport,
- 30-days warranty

