



PRAISTON Sp. z o.o.
ul. Górowska 32
64-100 Leszno
Polska

Biuro: +48 65 527 01 67
Serwis: +48 782 844 000
Fax: +48 65 527 01 67

E-mail: biuro@praiston.pl

Koordynator ds. sprzedaży
Krzysztof Wybieralski
+48 882 762 006

kw@praiston.pl



Halogen Light Source ATLANTECH AL 1 (Reconditioned)

- Condition: Reconditioned - Very Good,
- Made in Germany,
- Power input: 230 V,
- Frequency: 50 - 60 Hz,
- Power: 175 W,
- Compatible with rigid endoscopes,
- 2x fiber-optic output,
- Halogen OSRAM 15 V / 150 W,
- Xenon OSRAM XBO R 180 W / 45C,
- Weight: 5,6 kg,
- Dimensions: 21,5 x 40,5 x 13,5 cm,
- Technical Passport,
- 30-days warranty

