



PRAISTON Sp. z o.o.
ul. Górowska 32
64-100 Leszno
Polska

Biuro: +48 65 527 01 67
Serwis: +48 782 844 000
Fax: +48 65 527 01 67

E-mail: biuro@praiston.pl

Koordinator ds. sprzedaży
Krzysztof Wybieralski
+48 882 762 006

kw@praiston.pl



LID Diana Halogen light (New)

- New,
- Made in France,
- A very versatile halogen diagnostic lamp, with high power and excellent handling characteristics thanks to its ergonomic handle, which allows quick lamp placement and precise adjustment as required for heavy use,
- Heat-generating halogen bulb,
- Technical specifications:
 - Light intensity: 800 Lumens,
 - Light color: 3000°K* (neutral white),
 - Color rendering index: IRC 100/100,
 - Electricity consumption: 50 W,
 - Class 1 medical product,
 - 12V/50W 10° bulb: 516677,
 - Bulb life: minimum 5,000 hours,
 - Lamp power - 50 W (dual-color 12 V 50 W, OSRAM Decostar GU 5.3 ES SP 10° high efficiency (with UV filter),
 - Electrical protection: insulation class II,
 - Standards: IEC 60 601 -1/ -2-41 IEC 60 598-2-25,
 - Power cable length: 3 meters,
 - Available colors : white, black,
- The standard length of the lamp is 650 mm, for an extra charge you can purchase a lamp with a length of 1140 mm,
- Dimensions :
 - Lamp head dimension: 110 x 100 mm,
 - Dimension of the base: 69 x 69 x 115 mm,
 - Weight: 1.5 / 2.3 kg,
 - Length : flexible arm 650 / 1140 mm,
 - Inter-axis spacing (4 holes in the lamp base): 54.5 mm,
- Light field diameter :
 - 30 cm distance: 90,000 lux field illumination 5 cm
 - Distance 50 cm: 40,000 lux field illumination 7 cm,
 - Distance 100 cm: 10 000 lux field illumination 17 cm,
- Additional mounting accessories are required for the lamp , of your choice (at an extra charge):
 - Telescopic stand base 60-100 cm white metal, heavy,
 - Telescopic stand base 60-100 cm white metal, heavy -version with brakes in 2 wheels,
 - Telescopic stand base 90-130 cm white metal, heavy,
 - Telescopic stand base 90-130 cm metal white, heavy -version with brakes in 2 wheels,
 - Plain clamp - black,
 - Clamp for medical rails with vertical lamp outlet,
 - Universal clamp,
 - Wall bracket,
 - ARM wall bracket white (2x40cm),
 - ARM wall mount white (1x40cm),
 - Tabletop mount ARM white (1x60cm),
 - Metal base white / gray,
 - Plate with metal pipe in the middle ø16,
 - Plate with metal tube on the edge ø16,
 - Plate on ARM holder,
 - Female socket with adaptor plate Ø 16 mm x 27,
- It has a current Technical Passport issued,
- Warranty: 3 years,

If you have any questions, please do not hesitate to contact us!

In case you don't find the product you are interested in, please get in touch with us and we will do our best to find the perfect solution for YOU.

