



PRAISTON Sp. z o.o.
ul. Górowska 32
64-100 Leszno
Polska

Biuro: +48 65 527 01 67
Serwis: +48 782 844 000
Fax: +48 65 527 01 67

E-mail: biuro@praiston.pl

Koordinator ds. sprzedaży
Krzysztof Wybieralski
+48 882 762 006

kw@praiston.pl



Halogen Light Source OC-150-M (Reconditioned)

- Condition: Reconditioned - Good,
- Made in Ukraine,
- Power input: 230 V,
- Frequency: 50 - 60 Hz,
- Power: 220 V,
- 2x Halogen 100 W (Xenophot 64627 HLX EFP),
- Adjustable luminous intensity,
- 2x fiber-optic output: 7 mm,
- Air Pump,
- With handle,
- Dimensions: 37 x 31 x 15 cm.
- Technical Passport,
- Warranty: 30-days

