



PRAISTON Sp. z o.o.
ul. Górowska 32
64-100 Leszno
Polska

Biuro: +48 65 527 01 67
Serwis: +48 782 844 000
Fax: +48 65 527 01 67

E-mail: biuro@praiston.pl

Koordinator ds. sprzedaży
Krzysztof Wybieralski
+48 882 762 006

kw@praiston.pl



NGP 60 hf negatoscope (New)

- A brand new product,
- Made in Poland,
- The NGP 60 HF has a uniform screen, evenly illuminated at every point,
- The unit is easy to install and has a modern design,
- Powder-coated case allows the device to be kept clean,

• **Advantages of NGP 60 hf negatoscope:**

- Uniform screen, evenly illuminated at every point,
- Modern design of the device,
- Six-frame screen,
- The negatoscope has multiple certifications,
- Emits daylight with a color temperature of 6500°K,
- It has easy installation and service,
- It has a durable and modern powder-coated case,

• **Technical data:**

- Supply voltage: 230 V 50 Hz,
 - Power consumption: 390 W,
 - Screen luminance: 6000 cd/m²±25%,
 - Luminance regulation: NO,
 - Screen dimensions: 108 x 96 cm,
 - Number of frames: 6,
 - Protection class: I,
 - Dimensions: 1110 x 960 x 92 mm,
 - Weight: 31 kg,
- Provided with an up-to-date Technical Passport,
 - Guarantee: 12 months,

