



**PRAISTON Sp. z o.o.**  
ul. Górowska 32  
64-100 Leszno  
Polska

Biuro: +48 65 527 01 67  
Serwis: +48 782 844 000  
Fax: +48 65 527 01 67

E-mail: [biuro@praiston.pl](mailto:biuro@praiston.pl)

Koordinator ds. sprzedaży  
Krzysztof Wybieralski  
+48 882 762 006

[kw@praiston.pl](mailto:kw@praiston.pl)



## **NBVE 60 S germicidal lamp (New)**

- A brand new product,
- Made in Poland,
- **The device is 100% safe for people! It has a PZH certificate (National Institute of Hygiene),**
- Germicidal and virucidal flow-through lamp NBVE 60 S: without timer,
- The use of energy-efficient germicidal flow-through lamps of the NBVE series is one of the most effective and safest methods of disinfection,
- The modern design of the NBVE series lamps ensures that harmful UV-C radiation does not get off from the device, so it is safe to use the NBVE series lamps while patients and staff are in the room,
- These devices emit UV-C radiation with a wavelength of 253.7 nm. This radiation has the strongest biocidal properties and irreversibly inactivates bacteria, viruses, molds, fungi and all other microorganisms,
- The process of air purification through the energy-saving NBVE series flow-through lamps is applied by the forced circulation of air through the disinfection chamber, in which the germicidal radiators are located. This flow is performed by a fan built into the lamp.
- **Suitable for:**
  - Hospitals (surgery units, patients' rooms, emergency rooms, patients' wards, isolation rooms, A&E places, dirty linen rooms, etc.),
  - Clinics (doctor's and treatment rooms),
  - Laboratories,
  - Pharmacies,
  - The following industries: pharmaceutical, food-processing, cosmetics,
  - Hotel industry and gastronomy,
- **NBVE 60 S germicidal lamp's advantages:**
  - Mounting method: C- ceiling-mounted,,
  - A significant reduction in power consumption which enables to save from 200 to 300 PLN zloty. The discrepancy of this amount is due to the different lifetime of the lamps,
  - This is a flow-through germicidal lamp designed for air disinfection with staff and patients present in the room,
  - Forced air flow through the UV-C chamber,
  - Guarantees a consistently high level of air disinfection,
  - Designation: operating units, patients' rooms, laboratories, emergency rooms, waiting rooms, corridors and all crowded places. Generally speaking, wherever a high degree of microbiological cleanliness is required,
  - The case: acid-resistant sheet metal, which supports disinfection properties and allows to keep the device clean.
- **Technical data:**
  - Ceiling-mounted lamp,
  - Power supply voltage: 230 V 50 Hz,
  - Energy-saving – power consumption: 85 W,
  - UV-C emitting element: 2 x 30W,
  - Radiant's durability: 9000 h,
  - Fan's efficiency: 132 m<sup>3</sup>/h,
  - Disinfected capacity: 25 - 50 m<sup>3</sup>/h,
  - Operating range of the lamp: 10 - 20 m<sup>2</sup>,
  - Anti-schock safety class: I,
  - Case type: IP 20,
  - Chamber's dimensions: 1125 x 215 x 130 mm,
  - Dimensions: 1190 x 330 x 130 mm,
  - Weight: 8,5 kg,
- It has a valid Technical Passport,
- Guarantee: 12 months,

