



**PRAISTON Sp. z o.o.**  
ul. Górowska 32  
64-100 Leszno  
Polska

Biuro: +48 65 527 01 67  
Serwis: +48 782 844 000  
Fax: +48 65 527 01 67

E-mail: [biuro@praiston.pl](mailto:biuro@praiston.pl)

Koordinator ds. sprzedaży  
Krzysztof Wybieralski  
+48 882 762 006

[kw@praiston.pl](mailto:kw@praiston.pl)



## **X-ray machine SIEMENS SIREMOBIL COMPACT L (Reconditioned)**

- Condition: Reconditioned - Very good,
- Made in Germany (2002),
- Power input: 230 V,
- Frequency: 50 - 60 Hz,
- Power: 2,5 kVA,
- **X-ray generator / tube:**
  - Delivering Power (max.): 40 kV - 110 kV,
  - Fluoroscopy: 0,2 to 8,9 mA (max 550 W),
  - Tube current (max.): 0,2 to 12,2 mA (max 850 W),
  - Direct: 6,9 to 20 mA (max 1430 W),
  - Scope: 1 mAs to 150 mAs,
- **X-ray tube:**
  - Frequency: 15 kHz do 26 kHz,
  - Spot nominal value: 0,6,
  - Anode optical angle: 9°,
- Orbital movement: 130° (-40° to +90 °C),
- Wrap: +/- 190°,
- Horizontal movement: 20 cm,
- Vertical movement: 45 cm,
- Turnover range: +/- 12,5°,
- Immersion Depth: 73 cm,
- Laser sight: SIEMENS,
- **Comes with:**
  - 2 x LCD Neovo 19' Model: X-19AV,
  - Sealed control panel,
  - 2 shelves,
  - 2 handles,
  - On casters with breaks,
- **Printer SONY Model UP980CE:**
  - Condition: Reconditioned - Very good,
  - Made in Japan,
  - Power input: 230 V,
  - Frequency: 50 - 60 Hz,
  - Direct Thermal (DT), 256 shades of gray,
  - Multifunctional print,
  - Print Speed: CCIR: aprox. 12 sec EIA: aprox. 10 sec video,
  - Function SPLIT,
  - Adjustable brightness/contrast ratio,
  - CCTV /USG/ RTG,
  - Function Auto Cut,
  - Prints on blue transparent foil: Sony UPT-210BL,
  - Paper: Sony UPP-210HD or Sony UPP-210SE,
  - Video in/out,
  - Built-in display,
- Dimensions:
  - C-arm: 80 x 180 x 178 cm,
  - Control panel: 93,5 x 60 x 172,5 cm,
- Full documentation + manual,
- Technical Passport,
- Warranty: 30-days

