



PRAISTON Sp. z o.o.
ul. Górowska 32
64-100 Leszno
Polska

Biuro: +48 65 527 01 67
Serwis: +48 782 844 000
Fax: +48 65 527 01 67

E-mail: biuro@praiston.pl

Koordinator ds. sprzedaży
Krzysztof Wybieralski
+48 882 762 006

kw@praiston.pl



Autoclave EUROPA B EVO 24 (New)

New,
Made in Italy,
Class B autoclave,
Europa B Evo 24 is the latest generation of autoclave with several new features compared to the previous model Europa BXP,
The new control panel with its blue display is very modern and striking,
A real innovation is the new charging cap placed flush with the front of the front panel of the autoclave,
The autoclave has the following sterilisation cycles:
134°C - packaged and unpacked instruments,
121°C - packed and unpacked instruments,
fast cycle,
special cycle PRION, used for Creutzfeldt Jacobs disease,
night cycle - without the participation of the operator with automatic switching off at the end of work.
Advantages and features of the autoclave:
Maximum load per cycle 7.5 kg,
Built-in printer,
3 safety devices on the door: electromagnetic, electrical, dynamic,
Control card installed on board,
Graphic display,
Automatic barometric equalisation system,
Pump filling system with automatic stop when the tank is full,
Forced ventilation system built into the unit,
Safety tray holder to prevent contact between the load and the chamber,
P.I.D. system:
A system that continuously monitors and controls every process and function of the autoclave.
It diagnoses and reduces abnormalities and warnings (if any) in real time, guaranteeing reliability while minimising periods of downtime.
Technical data:
Sterilisation of batches type: A, B,
Chamber volume: 24 litres,
Useable volume: 18 litres,
Maximum pressure: 2.4 bar,
External dimensions: 510 x 395 x 790 mm,
Chamber dimensions: Ø 245 x 500 mm,
Weight: 58 kg,
Power supply: 230 V - 50 / 60 Hz,
Power consumption: 2.2 kW,
Equipment:
Trays with dimensions:
184 x 17 x 140 mm - 4 pcs,
184 x 17 x 286 mm - 4 pieces,
Tray stand with dimensions 192 x 200 x 470 mm,
Tray holder,
Plastic funnel with a diameter of 8 cm,
Pipe connector for backward discharge of waste water,
Hoses for drainage media:
For draining clean water,
For waste water disposal,
Rilsan hose,
Drainage hose,
Hose with filter for water filling,
Connection for water filling hose and plastic funnel,
Sponge for cleaning chamber and door seals,
Rear spacer,
Operating instructions in EN, IT, DE, SP, FR,
Quick reference guide for operation and installation,
Power cord,
It has a valid Technical Passport,
12 month warranty,
Financing options (Poland only): Instalments, Leasing, Loan

