



PRAISTON Sp. z o.o.
ul. Górowska 32
64-100 Leszno
Polska

Biuro: +48 65 527 01 67
Serwis: +48 782 844 000
Fax: +48 65 527 01 67

E-mail: biuro@praiston.pl

Koordinator ds. sprzedaży
Krzysztof Wybieralski
+48 882 762 006

kw@praiston.pl



NEOVO X 19 E Medical monitor (New)

- New,
- The X-19E is a rugged 19" display, perfect for environments where space is important. In high-traffic public areas, NeoV™ Glass optical glass protects the display from accidental damage. The attractive metal housing provides strength and durability for secure mounting anywhere. With built-in video support and multiple input options, the versatile X-19E provides a wide range of options for any environment. The new model features selectable gamma curves,
- Features and benefits of the NEOVO X 19 E monitor:
 - LED backlighting and 1920 x 1080 /1280 x 1024 / 1024 x 768 resolution,
 - NeoV™ optical glass and durable metal casing provide superior clarity and protection,
 - Anti-Burn-in™ technology prevents ghosting in the image,
 - Clear dynamic contrast ratio of 20,000,000:1,
 - Gamma correction for improved clarity and color quality,
 - PiP/PbP functions allow simultaneous viewing from multiple sources,
 - Image enhancement, non-interlaced / Noise reduction,
 - Flicker-free display - Flicker-free display technology reduces eye fatigue during prolonged use,
 - EcoSmart sensor detects ambient light conditions and automatically adjusts brightness levels,
 - Versatile connectivity: DisplayPort, HDMI, DVI, VGA,
 - Built-in speakers,
 - High-quality panel for high reliability and long product life,
 - V-standard wall mounting kit
 - VESA standard wall mounting kit,
 - Available colors: black, white,
 - Designed and developed for 24/7 continuous operation,
- Specifications:
 - Matrix:
 - Panel type: LED-Backlit TFT LCD (TN Technology),
 - Diagonal: 19.0",
 - Max. Resolution: SXGA 1280 x 1024,
 - Spot: 0.294 mm,
 - Brightness: 250 cd/m2,
 - Contrast ratio 20,000,000:1 (DCR),
 - Viewing angles (Pos/Pio): 170°/160°,
 - Color gamut: 16.7 M,
 - Response time: 3 ms,
 - Frequency (Pos/Pio):
 - Horizontal: 24 kHz - 83 kHz,
 - Vertical: 50 Hz - 75 Hz,
 - Inputs:
 - VGA: 15-Pin D-Sub x 1,
 - DVI: 24-Pin DVI-D x 1,
 - HDMI: 1,4 x 1,
 - DisplayPort: DisplayPort x 1,
 - Audio:
 - Input: Stereo Audio Jack (3.5mm),
 - Speakers: 2W X 2,
 - Power supply:
 - Power supply: External,
 - Current: DC 12V, 1.72 A,
 - Power consumption:
 - Power consumption: 14W (on),
 - Sleep mode: < 0.5W,
 - Off: < 0.3W,
 - NeoV™ optical filter:
 - Thickness: 3.0 mm (0.12"),
 - Reflectance ratio: < 1%,
 - Transparency factor: > 97%,
 - Surface hardness: 9H,
 - Operating Conditions:
 - Temperature: 0°C-40°C (32°F-104°F),
 - Humidity: 10%~90% (non-condensing),
 - Storage Conditions:
 - Temperature: -20°C-60°C (-4°F-140°F),
 - Humidity: 5%~95% (non-condensing),
 - Mounting:
 - VESA FPMPI: Yes (100 x 100 mm & 75 x 75 mm),
 - Stand:
 - Tilt: 0° to 22°,
 - Security:
 - Kensington™ security slot: Yes,
 - Dimensions:
 - Product with stand (W x H x D): 445.4 x 420.2 x 175.0 mm (17.5" x 16.5" x 6.9"),
 - Product without base (W x H x D): 445.4 x 383.9 x 64.5 mm (17.5" x 15.1" x 2.5"),
 - Package (W x H x D): 552.0 x 526.0 x 225.0 mm (21.7" x 20.7" x 8.9"),
 - Weight:
 - Monitor without stand: 6.0 kg (13.2 lb),
 - Monitor with stand: 6.8 kg (15.0 lb),
 - Monitor with packaging: 9.3kg (20.5 lb),
 - Regulatory Compliance:
 - Declarations and Directives: CE, LVD, WEEE, RoHS, REACH, EAC, FCC, UKCA,
 - Power supply certifications: Delta /ADP-40DD-B: CE, cUL/UL, RCM, WEEE, KCC, BSMI, EAC,
 - Accessories:
 - Supplied with the monitor; power adapter, power cord, VGA cable, audio cable, quick start guide, warranty card,
 - Optional accessories (at extra charge):
 - Table mount: DMC-01, DMC-02D, DMS-01Q, ES-02,
 - Ceiling mount (horizontal only): CMP-01 + WMK-03,
 - Wall mounts (horizontal only): WMA-01, WMK-01,
- Has a current Technical Passport issued,
- Warranty 36 months,

If you have any questions, please do not hesitate to contact us!

In case you don't find the product you are interested in, please get in touch with us and we will do our best to find the perfect solution for YOU.

