



PRAISTON Sp. z o.o.
ul. Górowska 32
64-100 Leszno
Polska

Biuro: +48 65 527 01 67
Serwis: +48 782 844 000
Fax: +48 65 527 01 67

E-mail: biuro@praiston.pl

Koordynator ds. sprzedaży
Krzysztof Wybieralski
+48 882 762 006

kw@praiston.pl



NEOVO X 22 E Medical monitor (New)

- New,
- The X-22E is a rugged 22” display, perfect for environments where space is important. In high-traffic public areas, NeoV™ Glass optical glass protects the display from accidental damage. The attractive metal casing provides strength and durability for secure mounting anywhere. With built-in video support and multiple input options, the versatile X-22E provides a wide range of options for any environment. The new model features selectable gamma curves,
- Features and benefits of the NEOVO X 22 E monitor:
 - LED backlighting and 1920 x 1080 /1280 x 1024 / 1024 x 768 resolution,
 - VA panel technology ensures accurate colors and offers high contrast ratio with wide viewing angles,
 - Anti-Burn-in™ technology prevents ghosting in the image,
 - NeoV™ optical glass and metal housing provide excellent ease of cleaning and protection,
 - Clear dynamic contrast ratio of 20,000,000:1,
 - PiP/PbP functions allow simultaneous viewing of images from multiple sources,
 - Gamma correction for improved clarity and color quality,
 - Image enhancement, non-interlaced / Noise reduction,
 - Flicker-free display - Flicker-free display technology reduces eye fatigue during prolonged use,
 - EcoSmart sensor detects ambient light conditions and automatically adjusts brightness levels,
 - Versatile connectivity: DisplayPort, HDMI, DVI, VGA,
 - Built-in speakers,
 - High-quality panel for high reliability and long product life,
 - VESA standard wall mounting kit,
 - Available colors: black, white,
 - Designed and developed for 24/7 continuous operation,
- Specifications:
 - Matrix:
 - Panel type: LED-Backlit TFT LCD (VA Technology),
 - Diagonal: 21.5",
 - Max. Resolution: FHD 1920 x 1080,
 - Spot: 0.248 mm,
 - Brightness: 250 cd/m2,
 - Contrast ratio 20,000,000:1 (DCR),
 - Viewing angles (Pos/Pio): 178°/178°,
 - Color gamut: 16.7 M,
 - Response time: 5 ms,
 - Surface treatment: High-resolution customizable, Anti-glare coating (haze 25%), 3H Hardness Coating,
 - Frequency (Pos/Pio):
 - Horizontal: 24 kHz - 83 kHz,
 - Vertical: 50 Hz - 75 Hz,
 - Inputs:
 - VGA: 15-Pin D-Sub x 1,
 - DVI: 24-Pin DVI-D x 1,
 - HDMI: 1,4 x 1,
 - DisplayPort: DisplayPort x 1,
 - Audio:
 - Input: Stereo Audio Jack (3.5mm),
 - Speakers: 2W X 2,
 - Power supply:
 - Power supply: External,
 - Current: DC 12V, 3.33 A,
 - Power consumption:
 - Power consumption: 16W (on),
 - Sleep mode: < 0.3W,
 - Off: < 0.2W,
 - NeoV™ optical filter:
 - Thickness: 3.0mm (0.12"),
 - Reflectance ratio: < 1%,
 - Transparency factor: > 97%,
 - Surface hardness: 9H,
 - Operating Conditions:
 - Temperature: 0°C-40°C (32°F-104°F),
 - Humidity: 10%~90% (non-condensing),
 - Storage Conditions:
 - Temperature: -20°C-60°C (-4°F-140°F),
 - Humidity: 5%~95% (non-condensing),
 - Mounting:
 - VESA FPMPI: Yes (100 x 100 mm & 75 x 75 mm),
 - Stand:
 - Tilt: 0° to 15°,
 - Security:
 - Kensington™ security slot: Yes,
 - Dimensions:
 - Product with base (W x H x D): 513.2 x 368.5 x 155.0 mm (20.2" x 14.5" x 6.1"),
 - Product without base (W x H x D): 513.2 x 324.3 x 56.2 mm (20.2" x 12.8" x 2.2"),
 - Package (W x H x D): 614.0 x 477.0 x 204.0 mm (24.2" x 18.8" x 8.0"),
 - Weight:
 - Monitor without stand: 6.2 kg (13.7 lb),
 - Monitor with stand: 6.7 kg (14.7 lb),
 - Monitor with packaging: 8.8 kg (19.4 lb),
 - Regulatory Compliance:
 - Declarations and Directives: CB, CE, WEEE, RoHS, REACH, EAC,
 - Power supply certifications: Delta /ADP-40DD-B: CE, cUL/UL, RCM, WEEE, KCC, BSMI, EAC,
 - Accessories:
 - Supplied with the monitor; power adapter, power cord, VGA cable, audio cable, quick start guide, warranty card,
 - Optional accessories (at extra charge):
 - Table mount: DMC-01, DMC-02D, DMS-01D, DMS-01Q, ES-02,
 - Ceiling mount (horizontal only): CMP-01 + WMK-03,
 - Wall mounts (horizontal only): WMA-01, WMK-01, WMK-03, PMK-01,
- Has a current Technical Passport issued,
- Warranty 36 months,

If you have any questions, please do not hesitate to contact us!
In case you don’t find the product you are interested in, please get in touch with us and we will do our best to find the perfect solution for YOU.

