



**PRAISTON Sp. z o.o.**  
ul. Górowska 32  
64-100 Leszno  
Polska

Biuro: +48 65 527 01 67  
Serwis: +48 782 844 000  
Fax: +48 65 527 01 67

E-mail: [biuro@praiston.pl](mailto:biuro@praiston.pl)

Koordynator ds. sprzedaży  
Krzysztof Wybierański  
+48 882 762 006

[kw@praiston.pl](mailto:kw@praiston.pl)



**Micfleye Mic-Fi camera (New)**

A new one,  
MICFIEYE is a very innovative handheld digital color camera with wireless Wi-Fi transmission,  
It's small, easy to use, lightweight and portable. It can be used with all major smartphones, tablets and even a computer,  
With the right software and apps, you can take pictures and record videos on your computer, smartphone or tablet.  
Features and benefits of the camera:  
Small, portable, lightweight,  
Easy to use,  
Wireless (Wi-Fi),  
The package includes:  
Wi-Fi Mic-Fi digital camera,  
USB power supply unit,  
USB cable,  
The user manual is in English,  
Additional accessories (extra charge):  
Standard 23 mm lens (MICFIEYE23),  
Microscope adapter 30 mm (MICFIEYE30),  
Microscope adapter 30.5 mm (MICFIEYE30.5),  
Camera head C-Mount F18 (MICFIEYEF18),  
Camera head C-Mount F15-25 (MICFIEYEF1525),  
Ring adapter 5 mm (MICFIEYERING),  
Technical data  
Camera type: Color CMOS camera,  
Sensor: 1/4" Imax CMOS  
Resolution: 1.3M Pixel,  
Image quality: HD,  
Lens standard: CCTV lens with C-CS mount,  
Optical functions:  
Gamma correction: Auto,  
Exposition: Auto,  
White balance: Auto,  
Black link: Auto,  
Avoiding flickering: Auto,  
Saturation of colours: Auto,  
A snapshot of a button: Yes for WiFi and USB mode,  
Dimensions: 36 mm (diameter) x 75 mm (length),  
Weight: 88g,  
WiFi standard: IEEE 802.11 b/g/n,  
Distance of WiFi transmission: ≥5M,  
Video resolution: 1.3MP: 320(H)x 240(V),640(H)x 480(V), 1280(H)x1024(V),  
Frame rate: 15 frames per second (1280 x 1024), 30 frames per second (640 x 480), 320 x 240 pixels,  
Frequency range: 2.400 ~ 2.4835GHz,  
Li-ion Battery: Continuous working time - about 2.5 hours,  
Power source: DC5.0V / 1A Use only USB wall adapters that are certified according to CE and/or FCC regulations,  
Power source: DC5.0V / 1A Use only USB wall adapters that are certified according to CE and/or FCC regulations,  
PC interface: USB 2. 0,  
Operating system support: MAC / Windows,  
MiniUSB Cable for recharging: 1.2m,  
Operating system: Windows, OS X, iOS, Android (can be used with Wi-Fi or USB),  
Application for Wi-Fi mode: WiFiMic-Fi:IOS/MAC/Android/Windows,  
Software for USB mode: USBMic-Fi-Windows/MAC,  
He has issued a valid Technical Passport,  
Warranty 12 months,  
Possibility of financing (only Poland): Instalments, Leasing, Loan, Translated with [www.DeepL.com/Translator](http://www.DeepL.com/Translator) (free version)

A new one,  
MICFIEYE is a very innovative handheld digital color camera with wireless Wi-Fi transmission,  
It's small, easy to use, lightweight and portable. It can be used with all major smartphones, tablets and even a computer,  
With the right software and apps, you can take pictures and record videos on your computer, smartphone or tablet.  
Features and benefits of the camera:  
Small, portable, lightweight,  
Easy to use,  
Wireless (Wi-Fi),  
The package includes:  
Wi-Fi Mic-Fi digital camera,  
USB power supply unit,  
USB cable,  
The user manual is in English,  
Additional accessories (extra charge):  
Standard 23 mm lens (MICFIEYE23),  
Microscope adapter 30 mm (MICFIEYE30),  
Microscope adapter 30.5 mm (MICFIEYE30.5),  
Camera head C-Mount F18 (MICFIEYEF18),  
Camera head C-Mount F15-25 (MICFIEYEF1525),  
Ring adapter 5 mm (MICFIEYERING),  
Technical data  
Camera type: Color CMOS camera,  
Sensor: 1/4" Imax CMOS  
Resolution: 1.3M Pixel,  
Image quality: HD,  
Lens standard: CCTV lens with C-CS mount,  
Optical functions:  
Gamma correction: Auto,  
Exposition: Auto,  
White balance: Auto,  
Black link: Auto,  
Avoiding flickering: Auto,  
Saturation of colours: Auto,  
A snapshot of a button: Yes for WiFi and USB mode,  
Dimensions: 36 mm (diameter) x 75 mm (length),  
Weight: 88g,  
WiFi standard: IEEE 802.11 b/g/n,  
Distance of WiFi transmission: ≥5M,  
Video resolution: 1.3MP: 320(H)x 240(V),640(H)x 480(V), 1280(H)x1024(V),  
Frame rate: 15 frames per second (1280 x 1024), 30 frames per second (640 x 480), 320 x 240 pixels,  
Frequency range: 2.400 ~ 2.4835GHz,  
Li-ion Battery: Continuous working time - about 2.5 hours,  
Power source: DC5.0V / 1A Use only USB wall adapters that are certified according to CE and/or FCC regulations,  
Power source: DC5.0V / 1A Use only USB wall adapters that are certified according to CE and/or FCC regulations,  
PC interface: USB 2. 0,  
Operating system support: MAC / Windows,  
MiniUSB Cable for recharging: 1.2m,  
Operating system: Windows, OS X, iOS, Android (can be used with Wi-Fi or USB),  
Application for Wi-Fi mode: WiFiMic-Fi:IOS/MAC/Android/Windows,  
Software for USB mode: USBMic-Fi-Windows/MAC,  
He has issued a valid Technical Passport,  
Warranty 12 months,  
Possibility of financing (only Poland): Instalments, Leasing, Loan

