



**PRAISTON Sp. z o.o.**  
ul. Górowska 32  
64-100 Leszno  
Polska

Biuro: +48 65 527 01 67  
Serwis: +48 782 844 000  
Fax: +48 65 527 01 67

E-mail: [biuro@praiston.pl](mailto:biuro@praiston.pl)

Koordynator ds. sprzedaży  
Krzysztof Wybieralski  
+48 882 762 006

[kw@praiston.pl](mailto:kw@praiston.pl)



## **Camera Micfiefy5m Mic-Fi (New)**

A new one,  
MICFIEYE5M is a very innovative handheld digital color camera with wireless Wi-Fi transmission,  
It's small, easy to use, lightweight and portable. It can be used with all major smartphones, tablets and even a computer,  
With the right software and apps, you can take pictures and record videos on your computer, smartphone or tablet.

Features and benefits of the camera:

Small, portable, lightweight,

Easy to use,

Wireless (Wi-Fi),

The package includes:

Wi-Fi Mic-Fi digital camera,

USB power supply unit,

USB cable,

The user manual is in English,

Additional accessories (extra charge):

Standard 23 mm lens (MICFIEYE23),

Microscope adapter 30 mm (MICFIEYE30),

Microscope adapter 30.5 mm (MICFIEYE30.5),

Camera head C-Mount F18 (MICFIEYEF18),

Camera head C-Mount F15-25 (MICFIEYEF1525),

Ring adapter 5 mm (MICFIEYERING),

Technical data

Camera type: Color CMOS camera,

Sensor: 1 / 2.5 "Imax CMOS,

Image quality: HD,

Resolution: 5M Pixel

Lens standard: CCTV lens with C-CS mount,

Optical functions:

Gamma correction: Auto,

Exposition: Auto,

White balance: Auto,

Black link: Auto,

Avoiding flickering: Auto,

Saturation of colours: Auto,

A snapshot of a button: Yes for WiFi and USB mode,

WiFi standard: IEEE 802.11 b/g/n,

Distance of WiFi transmission:  $\geq 5M$ ,

Video resolution: 1.3MP: 320(H)x 240(V), 640(H)x 480(V), 1280(H)x1024(V),

Frequency range: 2.400 ~ 2.4835GHz,

Li-ion Battery: Continuous working time - about 2.5 hours,

Power source: DC5.0V / 1A Use only USB wall adapters that are certified according to CE and/or FCC regulations,

Dimensions: 36 mm (diameter) x 75 mm (length),

PC interface: USB 2.0,

Operating system support: MAC / Windows,

MiniUSB Cable for recharging: 1.2m,

Operating system: Windows, OS X, iOS, Android (can be used with Wi-Fi or USB),

Application for Wi-Fi mode: Wi-FiMic-Fi:IOS/MAC/Android/Windows,

Software for USB mode: USBMic-Fi-Windows/MAC,

Software functions:

Wi-FiMic-Fi: shutter, video recording, calibration and measurement,

USBMic-Fi: Shutter, Video Recording, No Photo Time, Calibration and Measurement,

He has issued a valid Technical Passport,

Warranty 12 months,

Possibility of financing (only Poland): Instalments, Leasing, Loan

