



PRAISTON Sp. z o.o.
ul. Górowska 32
64-100 Leszno
Polska

Biuro: +48 65 527 01 67
Serwis: +48 782 844 000
Fax: +48 65 527 01 67

E-mail: biuro@praiston.pl

Koordinator ds. sprzedaży
Krzysztof Wybieralski
+48 882 762 006

kw@praiston.pl



Operating light LED EMALED 200 M (Mobile with battery) (New)

New,
German production,
Mobile lamp (mobile base with battery),
Advantages and characteristics of the lamp:
Mobile EMALED 200M lamp characterized by integrated emergency power supply and therefore can be used up to 24 hours without a network connection,
It works very well in examination and treatment rooms,
high mobility and good body positioning,
high contrast light and low energy consumption,
no moving parts in the lamp head,
shadowless lighting and good color reproduction,
low energy consumption of test light with a power of just 10 -15 W,
Long-life LEDs of minimum 50,000 hours provide low operating costs,
Low service costs and long service life for safe operation and low maintenance costs,
Aluminum powder-coated housing,
High mobility and good lamp body positioning,
Barely noticeable heating of the head of the lamp,
Natural reproduction of the wheel ditch,
3-step brightness adjustment,
Two auto clivable brackets are included (additional brackets can be ordered at any time),
Specifications:
Maximum light intensity (per 1 m): 50,000 lx,
Light intensity: 30 - 100 %,
Operating distance: 70 - 140 cm,
Color temperature: 4 500 K,
Color reproduction ratio 95 Ra,
Durability of LEDs 50,000 h,
Diameter 24 cm,
7 LEDs,
Fixed focal length,
Voltage main: 230 V,
Frequency 50 - 60 Hz,
10VA lamp head power,
1 pc lamp head weight,
total weight 37 kg,
a mobile stand with 230V power supply included, a rotating stand, a spring arm, a battery charger and head EMALED 200
It has issued the current Technical Passport,
Warranty 24 months

