



Dental compressor EKOM DK50-10 Z/M (without box, with membrane dryer) (New)

- New,
- Slovak production,
- **Technical data:**
 - Rated voltage: 230V / 50 (60) Hz
 - Frequency: 115V / 60 Hz
 - Power: 0.55 Kw
 - Number of dental set: 1
 - To power: one unit,
 - Tank capacity: 10l,
 - Number of dental set: 1
 - Mounted: without box,
 - Equipped with: with dryer,
 - Oil-free,
 - Compressor capacity (working pressure 5-7bar):
 - 75 l.min- 1/5 bar (50Hz)
 - 85 l.min- 1/5 bar (60Hz)
 - Tank capacity: 10 lit.
 - Operating mode: S1-100%
 - Air drying rate: dew point -20 ° C
 - Volume:
 - ≤ 65 dB [A] (50 Hz)
 - ≤ 67 dB [A] (60 Hz)
 - Weight: 44kg.
 - Dimensions (W x D x H): 544x350x553 mm
- Has a valid Technical Passport issued,
- 12 months warranty,
- Financing option (Poland only): Installments, Leases, Loans

