



PRAISTON Sp. z o.o.
ul. Górowska 32
64-100 Leszno
Polska

Biuro: +48 65 527 01 67
Serwis: +48 782 844 000
Fax: +48 65 527 01 67

E-mail: biuro@praiston.pl

Koordinator ds. sprzedaży
Krzysztof Wybieralski
+48 882 762 006

kw@praiston.pl



Dental compressor EKOM DK50-10 PLUS (without box) (New)

- New,
- Slovak production,
- **Technical data:**
 - Rated voltage: 230V / 50 (60) Hz
 - Frequency: 115V / 60 Hz
 - Power: 0.55 Kw
 - Oil-free,
 - Number of dental set: 1
 - Compressor capacity (working pressure 5-7bar):
 - 75 l.min- 1/5 bar (50Hz)
 - 85 l.min- 1/5 bar (60Hz)
 - Tank capacity 25 lit.
 - Operating mode: S1-100%
 - Volume:
 - ≤ 66 dB [A] (50 Hz)
 - ≤ 68 dB [A] (60 Hz)
 - Weight: 48 kg
 - Dimensions (W x D x H): 460x500x708 mm
 - Number of dental sets: 1
- Has a valid Technical Passport issued,
- 12 months warranty,
- Financing option (Poland only): Installments, Leases, Loans

