



PRAISTON Sp. z o.o.
ul. Górowska 32
64-100 Leszno
Polska

Biuro: +48 65 527 01 67
Serwis: +48 782 844 000
Fax: +48 65 527 01 67

E-mail: biuro@praiston.pl

Koordinator ds. sprzedaży
Krzysztof Wybieralski
+48 882 762 006

kw@praiston.pl



Dental compressor EKOM DK50 2V/M (without box, with membrane dryer) (New)

- New,
- Slovak production,
- **Technical data:**
 - Rated voltage: 230V / 50 (60) Hz
 - Oil-free,
 - Frequency: 3x400V / 50 Hz
 - Power: 1.1 kW, 1.2 kW (3x400 / 50)
 - To power: two units,
 - Number of dental sets: 2
 - Compressor capacity (working pressure 5-7bar):
 - 108 l.min- 1/5 bar
 - Tank capacity: 25 lit.
 - Operating mode: S1-100%
 - Volume:
 - ≤ 69 dB [A]
 - Weight: 63 kg / 61 kg (3x400 / 50),
 - Air drying rate: dew point -20 ° C
 - To power: two units,
 - Dimensions (W x D x H): 460x565x720 mm,
- Has a valid Technical Passport issued,
- 12 months warranty,
- Financing option (Poland only): Installments, Leases, Loans

