



Dental compressor EKOM DK50 2VS/M (with box, with membrane dryer) (New)

- New,
- Slovak production,
- **Technical data:**
 - Rated voltage: 230V / 50 (60) Hz
 - Frequency: 3x400V / 50 Hz
 - Power: 1.1 kW, 1.2 kW (3x400 / 50)
 - Compressor capacity (working pressure 5-7bar):
 - 108 l.min- 1/5 bar
 - Tank capacity: 25 lit.
 - Number of dental sets: 2
 - Oil-free,
 - To power: two units,
 - Operating mode: S1-100%
 - Volume:
 - ≤ 55 dB [A]
 - Weight: 101 kg / 99 kg (3x400 / 50)
 - Air drying rate: dew point -20 ° C
 - Dimensions (W x D x H): 560x675x877mm,
- Has a valid Technical Passport issued,
- 12 months warranty,
- Financing option (Poland only): Installments, Leases, Loans

