



PRAISTON Sp. z o.o.
ul. Górowska 32
64-100 Leszno
Polska

Biuro: +48 65 527 01 67
Serwis: +48 782 844 000
Fax: +48 65 527 01 67

E-mail: biuro@praiston.pl

Koordinator ds. sprzedaży
Krzysztof Wybieralski
+48 882 762 006

kw@praiston.pl



Dental compressor EKOM DK50 2x2V / 110 (without box) (New)

- New,
- Slovak production,
- **Technical data:**
 - Frequency: 3x400V / 50Hz
 - Rated voltage: 230V / 50 (60) Hz, 115V / 60Hz,
 - Power: 2x1,1 kW (115V / 60Hz)
 - Number of dental sets: 4
 - Compressor capacity (working pressure 5-7bar)
 - 280 l.min- 1 / 5bar
 - Tank capacity: 110l.
 - Operating mode: S1-100%
 - Power: four units,
 - Oil-free,
 - Volume:
 - ≤ 73 dB [A]
 - Dimensions (W x D x H): 1085x490x815 mm
 - Weight: 106 kg, 104 kg (3x400 / 50)
- Has a valid Technical Passport issued,
- 12 months warranty,
- Financing option (Poland only): Installments, Leases, Loans

