



Light Source ZTM AS-150 (Reconditioned)

- Used, very good technical condition
- Polish production,
- Power supply: 230 V,
- Frequency: 50-60 Hz,
- Power: 1.6 A,
- Adapted to rigid endoscopes,
- Halogen light,
- 15V 150W halogen bulb,
- Smooth regulation of light intensity ,,
- It has one fiber optic socket,
- Handle to move,
- **Included:**
 - Optical fiber length 180 cm,
- Dimensions: 32, x 27 x 14 cm,
- Cat 02,
- Has a valid Technical Passport issued,
- Warranty:
 - 6 months for the domestic market - Poland,
 - 1 month on the international market,
- Financing option (Poland only): Installments, Leases, Loans.

