



**PRAISTON Sp. z o.o.**  
ul. Górowska 32  
64-100 Leszno  
Polska

Biuro: +48 65 527 01 67  
Serwis: +48 782 844 000  
Fax: +48 65 527 01 67  
E-mail: [biuro@praiston.pl](mailto:biuro@praiston.pl)

Koordinator ds. sprzedaży  
Krzysztof Wybieralski  
+48 882 762 006  
[kw@praiston.pl](mailto:kw@praiston.pl)



## **SIEMENS ARCADIS VARIC x-ray machine (Reconditioned)**

Used, very good technical condition,

German production (2010),

Power supply: 230 V,

Frequency: 50/60 Hz,

Power: 2.3 kW,

It is mainly used in orthopedics, trauma and vascular surgery and urology,

X-ray intraoperative apparatus gives excellent imaging capabilities in the resolution of 1024 x 1024 (12 bits),

Orbital movement range: 130 °,

Image amplifier: 9',

Full digital video track,

High frequency generator with maximum pulse power: 2.3 kW,

EASY - acquisition system with automatic selection of dose, contrast and brightness,

The camera is equipped with a strong lamp (current up to 13 mA), whose thermal parameters enable its uninterrupted operation for over 50 minutes,

Memory: up to 60,000 images,

Full DICOM 3.0 functionality,

Precise imaging and excellent visualization,

Simple and intuitive operation,

Maximum flexibility in data processing,

True digital navigation thanks to NaviLink 2D,

High performance for demanding applications,

Uncompromising visualization performance,

Generator:

Rated power (GENERATOR X-RAY): 2.3 kW,

MA range (X-RAY TUBE): 1-150 in 23 steps,

Shutter function (MONITOR): 0.2-23 mA,

Kv range (X-RAY GENERATOR): 40,

Ma range (IMAGE SYSTEM): 0.2-23,

EXPOSURE TIME (MICROMANIPULATORS): 5-10 s,

Pulse fluoroscopy (X-RAY GENERATOR): yes,

ABS control (MONITOR): exposure, TV aperture, camera gain,

Aec (X-RAY GENERATOR): mAs,

Pulses per second (MONITOR): up to 15 s,

Arm C:

Reverse position (C-ARM): yes

Rotation (C-ARM): 130 (+90 / -40),

Depth (PA GANTRY): 73 cm,

Free space (C-ARM): 78 cm,

Vertical movement (RADIATION DETECTOR): 40 cm (motorized),

Horizontal shift (C-ARM): 20 cm,

Panning motion (C-ARM): 12.5,

A trolley with two high resolution monitors included

Height-adjustable monitors,

Arm dimensions C: 173 x 81 x 173 cm,

Case weight: 236 kg,

Truck weight with monitors: 180 kg,

Has a valid Technical Passport issued,

Warranty:

6 months for the domestic market - Poland,

1 month on the international market,

Financing option (Poland only): Installments, Leases, Loans

