



**PRAISTON Sp. z o.o.**  
ul. Górowska 32  
64-100 Leszno  
Polska

Biuro: +48 65 527 01 67  
Serwis: +48 782 844 000  
Fax: +48 65 527 01 67

E-mail: [biuro@praiston.pl](mailto:biuro@praiston.pl)

Koordinator ds. sprzedaży  
Krzysztof Wybieralski  
+48 882 762 006

[kw@praiston.pl](mailto:kw@praiston.pl)



## **LID Carla FOCUS LED light (New)**

- New,
- Made in France,
- For gynecological applications, ideally mounted on a low 40/60 cm telescopic stand PIR00555 or on our rail clamp ETRPM007 with horizontal lamp output, it allows working above/below the shoulder and thus illumination directed towards the pelvis without being disturbed by the location of the lamp (even when used in conjunction with a colposcope),
- Technical data:
  - Light intensity: 420 Lumens,
  - Light color: 4500 K (neutral white),
  - Color rendering index: IRC 95/100,
  - Power consumption: 4,5 W,
  - LED lifetime: minimum 50,000 hours,
  - Electrical protection: insulation class II,
  - Standards: IEC 60 601 -1/ -2-41 IEC 60 598-2-25,
  - Power cord length: 3 meters,
  - Available colors : white, black,
- The standard length of the lamp is 650 mm, for an extra charge you can purchase a lamp with a length of 1100 mm or 1230 mm,
- Dimensions :
  - Lamp head dimension: 60 x 100 mm,
  - Dimension of the base: 69 x 69 x 60 mm,
  - Weight: 1.2 / 1.6 / 2.1 kg,
  - Length : 650 / 1000 / 1230 mm,
- Diameter of the light field :
  - 30 cm distance: 90,000 lux field illumination 8 cm
  - Distance 50 cm: 35,000 lux field illumination 15 cm,
  - Distance 100 cm: 9 000 lux field illumination 25 cm,
- Additional mounting accessories are required for the lamp , of your choice (at an extra charge):
  - Telescopic stand base 60-100 cm white metal, heavy,
  - Telescopic stand base 60-100 cm white metal, heavy -version with brakes in 2 wheels,
  - Telescopic stand base 90-130 cm metal white, heavy,
  - Telescopic stand base 90-130 cm white metal, heavy - version with brakes in 2 wheels,
  - Ordinary clamp - black,
  - Clamp for medical rails with vertical lamp outlet,
  - Universal clamp,
  - Wall bracket,
  - ARM wall bracket white (2x40cm),
  - ARM wall mount white (1x40cm),
  - Tabletop mount ARM white (1x60cm),
  - Metal base white / gray,
  - Plate with metal pipe in the middle  $\varnothing 16$ ,
  - Plate with metal tube on the edge  $\varnothing 16$ ,
  - Plate on ARM holder,
  - Female socket with adaptor plate  $\varnothing 16$  mm x 27 mm,
  - Adapter plate male rod  $\varnothing 15$  mm x 30 mm,
- It has a valid Technical Passport issued,
- Warranty: 3 years,

If you have any questions, please do not hesitate to contact us!

In case you don't find the product you are interested in, please get in touch with us and we will do our best to find the perfect solution for YOU.

