



PRAISTON Sp. z o.o.
ul. Górowska 32
64-100 Leszno
Polska

Biuro: +48 65 527 01 67
Serwis: +48 782 844 000
Fax: +48 65 527 01 67

E-mail: biuro@praiston.pl

Koordynator ds. sprzedaży
Krzysztof Wybieralski
+48 882 762 006

kw@praiston.pl



Headlamp ZALIMP L-20 (Reconditioned)

Used, very good condition,

Polish production,

Power supply: 230 V,

Frequency: 50/60 Hz,

Power: 10 W,

The advanced optics provide uniform, exceptionally bright and warm lighting,

Lightweight, flexible cap, adjustable in width with detachable soft front cushion. It can be adjusted to fit any head,

Adjustable lighting angle,

The sets are included:

Headlamp with a wire and adapter for power supply and switch,

Additional cable with adapter for power supply and switch,

Spare frontal pad,

Power supply with 5 V / 6 V power switch,

The suitcase to carry the kit,

The manual in Polish,

Lamp dimensions: 19 x 31.5 cm,

Power supply dimensions: 6.3 x 13.5 x 5.1 cm,

The dimensions of the suitcase: 34.5 x 29.5 x 7 cm,

The weight of the set: 1.2 kg,

He has a current Technical Passport issued,

Warranty:

6 months for the domestic market - Poland,

1 month for the international market,

Possibility of financing (Poland only): Instalments, Leasing, Loan

