



**PRAISTON Sp. z o.o.**  
ul. Górowska 32  
64-100 Leszno  
Polska

Biuro: +48 65 527 01 67  
Serwis: +48 782 844 000  
Fax: +48 65 527 01 67

E-mail: [biuro@praiston.pl](mailto:biuro@praiston.pl)

Koordinator ds. sprzedaży  
Krzysztof Wybieralski  
+48 882 762 006

[kw@praiston.pl](mailto:kw@praiston.pl)



## **STERILAIR PRO air sterilizer (New)**

A new one,  
Italian production,  
Sterilair PRO is a device for air sterilization, eliminating all microorganisms, including spores,  
The air is directed to the sterilization chamber of the system, where irradiation completely eliminates microbiological load in the air,  
This device can operate continuously even in the presence of people and provides maximum operator protection. It is simple, quiet and ergonomic. Only Tecno-Gaz offers a sterilization program that is comprehensive, efficient, ergonomic and safe,  
The advantages of the air disinfection system:  
Reduced risk of contamination of the operator, as required by the Health Safety Act,  
Reduction or elimination of costs and loss of profits due to long sick leave,  
Reduce or eliminate risks to patients,  
Having a bacteriologically clean environment,  
The Sterilair PRO is an indispensable device with very low costs, but providing a service of high social utility,  
The device can be mounted on a rack (at an additional cost),  
Technical data:  
Dimensions:  
with wall bracket: 82 x 27 x 11 cm,  
with a stand: 107 x 33 x 28 cm,  
The weight:  
with a wall bracket: 12.5 Kg,  
with a stand: 15 kg,  
Power supply: 230 V 50 Hz,  
Power consumption: 150 W,  
Mode of operation: continuous,  
The flow: 120 m<sup>3</sup>/h,  
Noise level: 32 dB,  
Lamps: n.4 UV-C tubes 25W G13T8 (7 W UVGI),  
Wavelength: 253.7 nm,  
Ultraviolet: 69 µW/cm<sup>2</sup> at 1 m (per lamp),  
External emission of UV-C radiation: none,  
The equipment: Dustproof filter, electronic programmer,  
Headlamp: Aluminum,  
Lamp life: 9000 hours (1 year: 24 hours x 365 days),  
He has a current Technical Passport issued,  
Warranty 12 months

