



PRAISTON Sp. z o.o.
ul. Górowska 32
64-100 Leszno
Polska

Biuro: +48 65 527 01 67
Serwis: +48 782 844 000
Fax: +48 65 527 01 67

E-mail: biuro@praiston.pl

Koordynator ds. sprzedaży
Krzysztof Wybieralski
+48 882 762 006

kw@praiston.pl



NOUVAG Dispenser DP 30 Vario infiltration pump (New)

New,
Swiss production,
DP 30 is a universal pump used for tumescent anaesthesia, endovascular procedures, liposuction and others,
The DP 30 has a wide range of applications, wherever precise yet fast fluid application is required. It has been designed so that its parameters can be easily adapted to the treatment,
The percentage of infiltration is controlled by means of a rotary potentiometer and foot pedal (up to 17 l/min),
The Vario pedal allows you to increase the speed gradually, as you press the pedal, to a parameter limited by the setting on the control panel.
Similarly, decreasing as you let go of the pedal.
Advantages of the Dispenser DP 30 Vario infusion pump:
Best price/performance ratio,
Easy to operate with little maintenance,
Saves time compared to the time-consuming injection of traditional infiltration,
Infiltration performance is infinitely adjustable and precise,
Reliable and proven technology,
Ergonomic housing - the lightest and smallest housing in its class and easy to clean surfaces,
On / Off light - green LED indicates if the unit is on,
Integrated fluid container - a standard bottle of infiltration solution is conveniently hung from the plug-in mount.
Easy tube configuration - Wide opening compartment for easy tube setup,
Low noise pump drive - the infiltration tube is easy to integrate and the internal pump operates at a low noise level,
Front access to the pump - access to the pump with only one hand is done by pressing the button next to the display, i.e. without unintentional movement of the device,
Accurate pump performance - reproducible infiltration performance thanks to a scaled controller,
Standard equipment:
Control unit,
A set of wires,
Power cord,
Footswitch,
Technical data:
Liquid flow rate up to 17 l/min,
Power consumption 40 VA,
Power supply 115/230 V, 50-60 Hz,
Maximum pressure 1.5 bar,
Dimensions 260 x 250 x 110 mm,
Net weight 2.5 kg,
He has a valid Technical Passport issued
Warranty 12 months

